



Clinical Pictures (Aesthetic)



Indications

- Smart mode(Preset mode) at each treatment
- Real Depth of Penetration
- Skin Tightening &Lifting
- Short treatment time
- Easy to use narrow and not flat area by point type hand piece
- Treat upto SMAS layer by HIFU
- Non Surgical face lifting and tightening
- Face & Body(fat) treatment by one device

HIFU_VIOLA

Technical Specifications

Standard type	Functions
Frequency	4MHz, 7MHz
Max Energy	3.0J/cm ²
Cartridge	7MHz : 1.5mm, 3.0mm, 4.5mm - For Face 4MHz : 10mm, 13mm (option) - For Body & Fat
Pitch	1.0~2.0mm (0.1mm step)
Power Level	Adjustable 1~10 Level
Length	25mm, 20mm, 15mm
Spot Size	<3mm
LCD	10.2" True Color Touch

Point type	Functions
Frequency	7MHz
Max Energy	3.0J/cm ²
Cartridge	7MHz : 1.5mm, 3.0mm
Power Level	Adjustable 1~10 Level
Shot speed	1-4 shot / sec
Spot Size	<3mm
LCD	10.2" True Color Touch

ULTRA POWERFUL HIFU SYSTEM

VIOLA

2 Hand Pieces



From the deep SMAS of skin to the epidermis.

VARIOUS TREATMENTS AVAILABLE!



- Forehead
- Cheek
- Chin
- Neck
- Abdomen
- Arm



- Deep Wrinkle
- Special area
- Under Eyes
- Nasolabial fold
- Small area

Use freely from small to large area.

Cartridge type	D1.5	D3.0	D4.5	F10	F13
Frequency	7MHz	7MHz	7MHz	4MHz	4MHz
Depth	1.5mm	3.0mm	4.5mm	10mm (Fat)	13mm (Fat)
Point type	1.5mm	3.0mm			

Point type cartridges For Face : 1.5mm, 3.0mm



Point type Hand piece



Standard cartridges For Face : 1.5mm, 3.0mm, 4.5mm
For Body(Fat) : 10mm, 13mm



Standard Hand piece



Smart protocols prepared for face and body

